



Gooch & Housego

Connector Set for Q-Switch-Driver Series A22x, A23x, A24x, A25x, A27x, A28x, A29x

This accessory provides the connection of the analogue and digital modulation interface for the A22x, A23x, A24x, A25x, A27x, A28x, A29x Q-Switch driver series.

It comprises the fully shielded plug and 1 meter coaxial pigtailed. For details refer to the part list below. The RF connecting cable between the RF driver and the AOM as well as the wires for the control signals are not included.

Part List

Item	Qty.	Description	Part-No.	Manufacturer
1	1	Mixed contact Connector Sub-D 7W2	DAM-/W2P-K87	ITT Cannon
			FM7W2P-K120	FCT
2	2	Coaxial terminal pin, 50R, straight, male, for RG 316 or RG 174 coax cable	DM 53742-5001	ITT Cannon
			alternatively:	
			Coaxial terminal pin, 50R, straight, male, for RG 178 coax cable	DM 53742-5000 FMX005S102
3	1	Housing, shielded shell	DA 121073-150	ITT Cannon
			FKH2-A-E	FCT
4	2	Locking screw	250-8501-013	ITT Cannon
			FRS1/5-K190	FCT
5	2x 1.0 m	RF-Coax cable RG316B/U – mind the type variations of item 2!		
			alternatively:	
			RF-Coax cable RG174A/U – mind the type variations of item 2!	
	2x 1.0 m	alternatively:		
	2x 1.0 m	RF-Coax cable RG178B/U – mind the type variations of item 2!		

Ordering Code

Part-No. 508A00135



光技術をサポートする
株式会社オプトサイエンス
<http://www.optoscience.com>

東京本社 〒160-0014 東京都新宿区内藤町1番地 内藤町ビルディング
TEL:03(3356)1064 FAX:03(3356)3466 E-mail:info@optoscience.com
大阪支店 〒532-0011 大阪市淀川区西中島7-7-2 新大阪ビル西館
TEL:06(6305)2064 FAX:06(6305)1030 E-mail:osk@optoscience.com
名古屋営業所 〒450-0002 名古屋市中村区名駅2-37-21 東海ソフトビル
TEL:052(569)6064 FAX:052(569)8064 E-mail:ngo@optoscience.com