



PHASE DEMODULATOR

DQPSK Demodulator

ITF Labs' DQPSK Demodulator is comprised of two packaged and qualified All-Fiber delay line interferometers, constructed from two continuous lengths of Corning SMF28 fiber fused to form wavelength-insensitive 3dB couplers. This results in unparalleled insertion loss, fringe contrast, port imbalance and polarization-dependency performance. Phase tuning is achieved using heaters directly deposited on the optical fiber of each interferometer, providing minimal power consumption and fast rise times.

This device is offered in a compact, stable and reliable package. Internally the DPSK has successfully completed qualification testing to Telcordia's GR-1221-CORE central office requirement and is also fully compliant with RoHS requirements. Field data indicates a reliability rate of less than 100 FIT at a 60% confidence level. Free from resonance below 2 kHz, the device can operate in the presence of ambient vibration. Connectorization is available as an option, with matched pigtail length down to 0.5ps accuracy.

For more information on this or other products and their availability, please contact our customer service at **514.748.4848** (Int'l) / **1.888.922.1044** (Canada & USA only) or via e-mail at info@itflabs.com



KEY FEATURES

- 10, 20, 30, 40 GHz and Custom Rates
- Near Zero PDL and PMD
- Tunable
- Work in C & L Bands
- Very Low PDF
- Low Excess Loss & High Isolation



光技術をサポートする
株式会社オプトサイエンス

<http://www.optoscience.com>

東京本社 〒160-0014 東京都新宿区内藤町1番地 内藤町ビルディング
TEL:03(3356)1064 FAX:03(3356)3466 E-mail: info@optoscience.com
大阪支店 〒532-0011 大阪市淀川区西中島7-7-2 新大阪ビル西館
TEL:06(6305)2064 FAX:06(6305)1030 E-mail: osk@optoscience.com
名古屋営業所 〒450-0002 名古屋市中村区名駅2-37-21 東海ソフトビル
TEL:052(569)6064 FAX:052(569)8064 E-mail: ngo@optoscience.com

PHASE DEMODULATOR

DQPSK Demodulator

SPECIFICATIONS

| PARAMETERS (1) & (7) | STANDARD CONFIGURATIONS | | | |
|-----------------------------------------|-------------------------|----------|----------|----------|
| Free Spectral Range | 10 GHz | 20 GHz | 30 GHz | 40 GHz |
| Isolation | 28 dB | | | |
| PDF (2) | 0.22 GHz | 0.45 GHz | 0.50 GHz | 0.55 GHz |
| Operating Wavelength | 1530 - 1610 nm | | | |
| Peak Insertion Loss (3) | <3.8 dB | | | |
| Differential Delay between Pigtails (4) | 0.5 ps | | | |
| Heater Resistance | 375 Ω | | | |
| Tuning Rise Time (5) | 100 - 300 ms | | | |
| Tuning Fall Time (5) | 100 - 320 ms | | | |
| Operating Case Temperature | 0 - 65° C | | | |
| Reliability (6) | < 100 FIT | | | |

- (1) All specs are typical values only.
(2) Δf between polarization eigenstates – more details available upon request.
(3) Includes wideband 3dB splitter to each delay line.
(4) Delay difference between ports 1 & 2, 3 & 4.
(5) τ such that $\Delta \varphi \propto 1 - e^{-t/\tau}$.
(6) Random fit rate. Qualified Telcordia's GR-1221-CORE central office (except for the 2.5 GHz unit).
(7) All measurements are "worst case" values over operating band of both ports.

Note: two delay line interferometers for aggregate bitrate of twice the FSR.

ORDERING INFORMATION

ITF Labs can also develop custom multimode power combiners to meet a wide range of technical requirements.



ITF Labs

400 Montpellier Blvd
Montreal, Quebec H4N 2G7 CANADA

Tel: 514.748.4848

Fax: 514.744.2080

1.888.922.1044

www.itflabs.com info@itflabs.com