

Co²⁺:Spinel - Passive Q-Switch

Passive Q-switches or saturable absorbers generate high power laser pulses without the use of electro-optic Q-switches, thereby reducing the package size and eliminating a high voltage power supply. Co²⁺:Spinel (MgAl₂O₄) is the material of choice for the important eye-safe wavelengths near 1.5 microns. It has useful absorption that covers 1.2 to 1.6 micron laser transitions. Spinel is a hard, stable crystal that polishes well.

Cobalt substitutes readily for magnesium in the Spinel host without the need for additional charge compensation ions. A convenient measure of the Co²⁺ concentration is the low power absorption coefficient α at, for example, 1533 nm, a typical wavelength for Erbium phosphate glass. SYNOPTICS grows crystals for passive Q-switches with α values from about 0.5 to 3 cm⁻¹. The actual Co²⁺ ion density N in the crystal can be calculated from $N = \alpha / \frac{1}{2} \sigma_{GSA}$ where $\frac{1}{2} \sigma_{GSA}$ is the ground-state absorption cross-section with a value¹ of 3.5 x 10⁻¹⁹ cm². This absorption is high enough to permit Q-switching of Erbium glass without intracavity focussing.

Passive Q-switches are typically specified by the low power Optical Density (or %T) at the laser wavelength. SYNOPTICS measures the α value in the crystal and adjusts the part thickness to the optical density specified. Thickness is therefore a free parameter, but typically 1 - 5 mm.



光技術をサポートする
株式会社オプトサイエンス
<http://www.optoscience.com>

東京本社 〒160-0014 東京都新宿区内藤町1番地 内藤町ビルディング
TEL:03(3356)1064 FAX:03(3356)3466 E-mail:info@optoscience.com
大阪支店 〒532-0011 大阪市淀川区西中島7-7-2 新大阪ビル西館
TEL:06(6305)2064 FAX:06(6305)1030 E-mail:osk@optoscience.com
名古屋営業所 〒450-0002 名古屋市中村区名駅2-37-21 東海ソフトビル
TEL:052(569)6064 FAX:052(569)8064 E-mail:ngo@optoscience.com

NORTHROP GRUMMAN

Space Technology

SYNOPTICS

Specifications

SYNOPTICS Standard

Orientation:	<100>
Surfaces:	flat / flat
Coatings:	AR < 0.25% at 1533 nm
Damage Threshold:	> 500 MW / cm ²

Customer Values

Diameter :	typical: 5 - 10 mm
Optical Density: at 1064 nm	typical: 0.70, 0.80, 0.90

References

1. K.V. Yumashev, Applied Optics **38**, No. 30 (1999) 6343-6346.

NORTHROP GRUMMAN

Space Technology

SYNOPTICS